## SC Johnson PROFESSIONAL A family company<sup>™</sup>

# **Deb Workplace Dispensers**

#### PRODUCT DESCRIPTION

Unique range of 1 litre, 2 litre and 4 litre closed, sealed cartridge dispensers that meet the distinct needs of any workplace and public facility environment.

#### USAGE

For exclusive use with Deb skin care products to create tailored skin care and hand hygiene programmes.

#### METHOD OF USE

Large, 'easy-push' buttons dispense a controlled dose of product appropriate for the application required. Empty cartridges are easily replaced in seconds.



FEATURES	BENEFITS			
Colour-coding	Easy visual identification of product type to encourage correct product usage and compliance.			
Usage illustrations	Simple to understand and language neutral to show best practice method of use; ideal for multinational workforces.			
Guaranteed for life	All Deb dispensers are manufactured from durable plastic components and rigorously tested for high usage environments, providing assurance of quality and longevity.			
BioCote® protected button	BioCote® antimicrobial protection technology is incorporated at the time of manufacture into the plastic buttons of all Deb manually operated, wall-mounted skin care dispensers. The button is the primary contact point for people using these dispensers and BioCote® technology provides life-long antimicrobial protection to inhibit the growth of a broad spectrum of bacteria and moulds that could potentially cause illness.			
Large push buttons	Minimises the operation force required to allow easy use by hand or elbow; suitable in hygiene- sensitive areas.			
Fixed product dose	Delivers the exact amount required, controlling usage and reducing waste.			
Unique locking mechanism	Helps prevent unauthorised access, pilferage and product contamination.			
Sight Glass	Provides visibility of the level of product in the cartridge which helps identify when product needs replacing.			
Simple cartridge replacement	Designed for exclusive use with Deb skin care system products to enable cartridges to be replaced in seconds, reducing maintenance time and costs.			
Hygienic, airless cartridges	The ultrasonically sealed cartridge and pump mechanisms prevent the ingress of air into the cartridge during use to help prevent product contamination and ensure 'fresh' product is dispensed every time.			
Minimal waste	The air-tight cartridges are designed to collapse to minimise product waste.			

### DEB STOKO SKINCARE SYSTEM<sup>™</sup> DISPENSER RANGE

STOCK CODE	DISPENSER	CARTRIDGE CAPACITY	DIMENSIONS (MM)	SHOT SIZE	APPLICATIONS PER CARTRIDGE
PRO1LDSEN	Deb Stoko Protect	1 Litre	233H x 130W x 115D	1.0ml	1,000
SUN1LDSEN	Deb Stoko Sun Protect	1 Litre	233H x 130W x 115D	1.0ml	1,000
LGT1LDSEN	Deb Stoko Cleanse Light	1 Litre	233H x 130W x 115D	1.0ml	1,000
LGT2LDPEN	Deb Stoko Cleanse Light	2 Litre	290H x 163W x 145D	4.5ml	444
LGT4LDREN	Deb Stoko Cleanse Light	4 Litre	345H x 175W x 150D	4.5ml	889
SHW1LDSEN	Deb Stoko Shower	1 Litre	233H x 130W x 115D	1.0ml	1,000
SHW2LDPEN	Deb Stoko Shower	2 Litre	290H x 163W x 145D	4.5ml	444
SHW4LDREN	Deb Stoko Shower	4 Litre	345H x 175W x 150D	4.5ml	889
HVY2LDPEN	Deb Stoko Cleanse Heavy	2 Litre	290H x 163W x 145D	4.5ml	444
HVY4LDREN	Deb Stoko Cleanse Heavy	4 Litre	345H x 175W x 150D	4.5ml	889
ULT2LDPEN	Deb Stoko Cleanse Ultra	2 Litre	290H x 163W x 145D	4.0ml	500
ULT4LDREN	Deb Stoko Cleanse Ultra	4 Litre	345H x 175W x 150D	4.0ml	1,000
ANTILDSEN	Deb Stoko Cleanse Antimicrobial	1 Litre	233H x 130W x 115D	0.70ml foam 1.5ml foam 1.0ml lotion	1,429 foam 667 foam 1,000 lotion
ANT2LDPEN	Deb Stoko Cleanse Antimicrobial	2 Litre	290H x 163W x 145D	0.70ml foam 1.5ml foam	2,857 1,333
WRM1LDSEN	Deb Stoko Cleanse Washroom	1 Litre	233H x 130W x 115D	0.70ml foam	1,429
WRM2LDPEN	Deb Stoko Cleanse Washroom	2 Litre	290H x 163W x 145D	0.70ml foam	2,858
SAN1LDSEN	Deb Stoko Sanitise	1 Litre	233H x 130W x 115D	0.75ml foam 1.5ml foam	1,429 667
RES1LDSEN	Deb Stoko Restore	1 Litre	233H x 130W x 115D	1.0ml	1,000
GPF3LWHI	Deb Stoko Cleanse Heavy FOAM	3.25 litre	345H x 175W x 165D	3ml foam	1,083





**PRO1LDSEN** 









SUN1LDSEN

LGT2LDPEN

SHW1LDSEN

HVY2LDPEN



ANT1LDSEN







INF01CON



WRM1LDSEN







GPF3LWHI





This information and all further technical advice is based upon our present knowledge and



SC Johnson Professional Ltd. Denby Hall Way Denby Derbyshire DE5 8JZ UK Tel: +44 (0) 1773 855100 www.scjp.com

with regard to existing third party intellectual property rights, especially patent rights. In particular, no warranty, whether express or implied, or guarantee of product properties in the legal sense is intended or implied. We reserve the right to make any changes according to technological progress or further developments.

experience. However, it implies no liability or other legal responsibility on our part, including

 $\circledast$  = is a registered trademark of SC Johnson Professional Ltd. or one of its subsidiaries © SC Johnson Professional Ltd.

PROFESSIONAL

A family company